

Fitting for top-running wooden doors up to 160 kg (352 lbs.), with surface mounted running track or running track flush with the ceiling. Ceiling mounting. Minimal installation height.



Installation examples





Set for 1 wooden door up to 160 kg (352 lbs.)

				No.
Hawa Junior 160 B, for 1 door			11695	
Hawa Junior 160 B, with 2 track stoppers, for 1 door			26044	
Set consisting	of:	11695	26044	No.
	Running gear, 2-wheeled, plastic, with suspension bolt M14	2	2	10424
5	Stopper, with adjustable retention spring	1	2	10639
R ational Astronomy	Suspension profile, with plate M14	2	2	10491
	Cover cap for glass suspension profile, plastic, anthracite	2	2	20907
	Bottom guide, zero tolerance, groove width 14 mm (9/16"), plastic	1	1	14711
9	Rubber buffer, 29x11 mm (1 5/32"x7/16"), for screw fixing	1	1	13114

Running tracks

	mm (inch)	No.
Running track, aluminum, anodized, pre-drilled	3,000 (9' 10 1/8 '')	24608
	4,000 (13' 1 15/32'')	24607
	5,000 (16' 4 27/32'')	24606
	6,000 (19' 8 7/32'')	24605
	cut to size	24609

Guide tracks

	mm (inch)	No.
Guide track, for groove mounting, plastic, 5-piece set	3,000 (9' 10 1/8 '')	14963

Suspension profiles

For better distribution of the door weight, we recommend a continuous suspension profile for heavy sliding doors.


		mm (inch)	No.
	Multi purpose suspension and	6,500 (21' 3 29/32'')	10346
	retainer profile, aluminum, anodized, pre-drilled	cut to size	10347

Accessories

	No.
Bottom door stopper, with centering, stainless steel look	21473
Bottom door stopper, with centering, chrome-plated, matt	20773
Connecting pins to profiles, 2-piece set	21347

Hawa Confort 160

The convenient solution for inadequate fastening options in brittle sub-floors or in the area of floor heating. This bottom guide is mounted on the wall. Details and accessories from page 476.



Accessories

- Hawa Junior bottom guides for wall mounting from page 476
- Lock solutions from page 479
- General accessories from page 487

Planning/execution

Further information about the product can be found on www.hawa.com.