








Drawer inner drawer – K		Web code	Drawer	DQCLQM
			Inner drawer	DQCOJY

Planning		Drilling distances – front – EXPANDO knock-in	Installation dimensions – back
Space requirement in cabinet	Installation dimensions – front – screw-on		
 * +2 mm with BLUMOTION * +3 mm for inner drawer with BLUMOTION	 Drawer Inner drawer FA Front overlay * +2 mm with BLUMOTION * +3 mm for inner drawer with BLUMOTION	 Drawer * +2 mm with BLUMOTION * +3 mm for inner drawer with BLUMOTION	


Cutting – 16 mm chipboard

	Chipboard back 103 mm
	Base Drawer NL – 2 mm Inner drawer NL – 18 mm
	Front Inner drawer 93 mm
LW	Internal cabinet width
NL	Nominal length



LW	Internal cabinet width
KB	Cabinet width

Base – quick assembly version



	X (mm)
Drawer	69
Inner drawer	53

Reference pages

Overview	339	Assembly, removal and adjustment
Accessories	354	
BLUMOTION for METABOX 320	357	
Cabinet profile fixing positions	361	
Blum services	602	
More technical details	708	

Short URL
www.blum.com/a390